

VA - POLYPREP 3KB

3-Chamber Polymer Preparation Solution



VA - POLYPREP 3KB



DESIGN

- PPH Preparation, Riping and Dosing Chambers with Level Sensors.
- Powder Polymer Dosing Funnel and Agitators made of Stainless Steel.
- Water Connection made of Brass, Isolating Valve of Stainless Steel.
- Solution Water and Liquid Polymer Connection made of PVC.
- Switch Cabinet with PLC and TOUCH PANEL.
- Available with 1000, 2000, 4000, 6000 and 800 Litres capacitry (other sizes on request)

VA - POLYPREP can be operated using either powder or liquid polymer. Slowly running agitators made of stainless steel prepare a ready-to-use solution in the preparation and ripening chambers which is then discharged into the dosing chamber. From there, the solution can be withdrawn continuously. The whole process runs automatically and is controlled via a userfriendly TOUCH PANEL on the switch cabinet.



W + AT GmbH

Wasser + Abwassertechnik GmbH Lunzerstraße 64 • A-4031 LINZ Phone ++43/(0)732/6989-8116 o. 6149 Mobile ++43/(0)664/4501028 wat-gmbh@w-at.at

